




Thank you for purchasing our products.
Spooky Lumino color variations are: BLUE / RED / GREEN
Please read this instruction carefully before applying the colors.

Spooky Lumino Color

USER INSTRUCTIONS

Wavelength 365 nm Back Light recommended. If other BL wavelength is used, might not luminate correctly.



After light emission



Painting instructions

1. Pretreat the old coating with 500~800 sanding papers.
2. After sanding, apply Spooky paint straight – apply it straight / undiluted.
Apply 4~6 coats half wet. Recommended spray gun nozzle: 0.8 ~1.5mm, spray pressure 1-2 round, max flash.
Wait around 5 minutes after each coat.
*** For Spooky Red, make sure to check with the UV light on every 8th half wet coating.**
3. After drying Spooky coating, apply single or double stage with hardener clear of your choice.
Wait 5~10 minutes each time top coat is applied. Repeat the process 1 or 2 times to finish.

*Make sure to take the interval (waiting time) when applying the top coat.
Spooky may smudge without taking enough interval time.
After applying the clear top coat, finish with regular polishing procedure.

Precautions for use:

Get medical attention immediately. in case feeling sick, ill, unwell while using the product.
Promptly wash eyes with plenty of water if inhaled or gets in the eyes. Get medical help if irritation continues.
Wear protective clothes such as masks, protective gloves and avoid inhaling the vapor for a long time.
Keep the product in the cold place in order to avoid fire hazard.



Signal Inc., SHOW UP Division, 2-6-8 Aoshinke Mino Si Osaka, Japan 562-0024

<https://www.showup.jp/spookyE.html>